



D-2 Incorporated

Precision Industrial Sensors

JF-WA1 Hydro-Light Accessories

ASTM Test Method D-2624 Listed

JF-WA1-CC Hydro-Light Rugged Carrying Case



The JF-WA1-CC is a Carrying Case that is designed to fit the JF-WA1 Hydro-Light and all required accessories for running the ASTM D-3240 Test in the field. This case makes the Hydro-Light much easier to transport to your test site. Customizable foam inserts allow the user to arrange equipment as they wish or follow our recommended chart. The Carrying Case is very hard, durable and most importantly the case is completely waterproof when closed. So don't be afraid to check it at the airport, or strap it to your tank.

JF-WA1-BAT Portable Battery Pack



The JF-WA1-BAT is a portable battery pack for powering the JF-WA1 Hydro-Light. The battery connects via a JF-WA1-USB cable, which allows for field testing. (cable sold separately)
The battery pack can supply 12000 mAh with a recharge input time of 8 – 10 hours. With each JF-WA1 test taking only three seconds; this allows countless uses before the portable battery needs to be recharged.

JF-WA1-USB Cable

The JF-WA1-USB is a Standard A to 5 Pin Mini B, 2' USB Cable. It is used to either power or serially communicate with the JF-WA1 Hydro-Light.

JF-WA1-VS Calibration Verification Shuttle

The verification shuttle has two standards fixed pads in one pad holder. The shuttle is marked with a high value on one side and a low value on the other. This allows you to verify the calibration over two points in a matter of ten seconds. It is supplied with the JF-WA1 and is also sold as a separate accessory.

A480-001R- June 15, 2012

**19 Commerce Park Road
Pocasset, MA 02559
(508) 329-2046
www.D-2inc.com**